

SEPARATION TECHNOLOGIES

ION EXCHANGE RESINS

DUOLITE A 101 D

ENGINEERING DATA SHEET COUNTER-CURRENT REGENERATION



Duolite a 101 D is a type 1 strong base Anion Exchange Resin. These data provide information to calculate the silica leakage and operating capacity of Duolite A 101 D used with Counter-current regeneration. The general properties of Duolite A 101 D are described in the Product Data Sheet.

SILICA LEAKAGE

The average silica leakage is obtained by multiplying the basic leakage value from Table 1 by the correction factors A,B and C from Tables 2 to 4. For Silica to Total Anion ratio above 75% refer Table No. 11 Silica leakage will increase approximately by 15% for every 1 ppm Sodium leakage from preceding cation unit

$$\text{Leak} = \text{Leak}_0 \times A \times B \times C$$

TABLE 1 : Basic Silica Leakage versus NaOH regenerant level

NaOH g / L	Leakage ppm SiO ₂ (Leak ₀)
40	0.012
50	0.010
60	0.008
70	0.006
80	0.005
100	0.003
120	0.002

TABLE 2 : Leakage Correction Factor A versus Silica to Total Anions ratio.

SiO ₂ %	Factor A
1	0.2
5	0.5
10	1.0
25	2.5
50	5.0
75	10.0

TABLE 3 : Leakage Correction Factor B versus water Temperature

Water °C	Factor B
5	0.7
10	0.8
15	1.0
25	1.5
35	2.3
45	3.3

TABLE 4 : Leakage Correction Factor C versus Regenerant Temperature

NaOH °C	Factor C
10	1.65
15	1.37
25	1.00
35	0.76
45	0.58
50	0.50

TABLE 5 : Suggested Operating Conditions

Maximum operating temperature _____	60°C (OH ⁻) 100°C (Cl ⁻)
Minimum bed depth _____	1000 mm **
Service flow rate _____	5 to 40 BV* / hr
Maximum linear velocity _____	50 m / hr
Regenerant _____	NaOH
Level _____	40 to 160 g / L
Flow rate _____	2 to 10 BV/ hr (minimum contact time : 30 minutes)
Concentration _____	3% to 5%
Slow rinse _____	Minimum 2 BV at regeneration flow rate
Fast rinse _____	Same as service flow rate.

* 1 BV (Bed Volume) = 1 m³ solution per m³ resin

** For selection of lower bed depth please contact Auchtel technical representative

Influent Limitations

Free chlorine - Nil

OPERATING CAPACITY

The operating capacity of Duolite A 101 D is obtained by multiplying the basic capacity value from Table 6 by the correction factors D to G from Tables 7 to 10.

$$\text{Cap} = \text{Cap}_0 \times D \times E \times F \times G$$

TABLE 6 : Basic capacity versus NaOH regenerant level (Counter - current regeneraion)

NaOH g/L	Capacity eq/L (Cap ₀)
40	0.62
50	0.67
60	0.70
70	0.73
80	0.76
100	0.79
120	0.82

TABLE 7 : Capacity Correction Factor D versus Sulphate to Total Anions Ratio.

SO ₄ %	Factor D
0	0.92
25	0.96
50	1.00
75	1.04
99	1.08

TABLE 8 : Capacity Correction Factor E versus CO₂ to Total Anions Ratio.

CO ₂ %	Factor E
0	0.97
20	1.00
30	1.02
50	1.05
75	1.08
99	1.12

TABLE 9 : Capacity Correction Factor F versus Silica to Total Anions Ratio and NaOH Temperature

% SiO ₂	Factor F		
	20 °c	25 °c	35 °c
5	0.96	0.98	0.99
25	0.90	0.94	0.96
50	0.85	0.87	0.90
75	0.80	0.82	0.88

TABLE 10 : Capacity Correction Factor G versus Silica Endpoint (D SiO₂ = difference between average leakage and endpoint)

SiO ₂ (ppb)	Factor G
50	0.90
100	0.95
200	1.00
300	1.04

SAFE HANDLING INFORMATION

A material Safety Data Sheet, Material handling & storage sheet are available for Duolite products. To obtain a copy contact Auchtel representative

CAUTION

Acid and basic regenerant solutions are corrosive and should be handled in a manner that will prevent eye and skin contact. Nitric acid and other strong oxidizing agents can cause explosive type reactions when mixed with Ion Exchange Resins. Proper design of process equipment to prevent rapid buildup of pressure is necessary if use of an oxidizing agent such as nitric acid is contemplated. Before using strong oxidizing agents in contact with Ion Exchange Resins, consult sources knowledgeable in the handling of these materials.

The suggestions and data in this bulletin are based on information we believe to be reliable. They are offered in good faith, but without guarantee, as conditions and methods of use of our products are beyond our control. We recommend that the prospective user determine the suitability of our materials and suggestions before adopting them on a commercial scale. The Company maintains a policy of continuous development and reserve the right to amend any specification without notice. DUOLITE is a trademark of Rohm and Hass Company, Philadelphia, U.S.A. and Auchtel Products Ltd. are users of the same in India.

**Auchtel Products Ltd., 142 C, Victor House, N.M. Joshi Marg, Lower Parel(w), Mumbai-400 013
Tel. 91-22-493 3975, Fax. 91-22-493 9755, 497 4211 E-mail - auchtel@vsnl.com**